



Fluoropolymeric heat shrinkable tubes

Produced: with inner diameter after shipment/after setting – from 2.0/1.2 mm to 40/20mm

Inner diameter, mm				Wall thickness after heating (setting), mm	
nominal value, mm		deviation limit, mm		nominal value, mm	deviation limit, mm
after shipment	after heating (setting)	after shipment	after heating (setting)		
2,0	1,2	±0,2		0,70	±0,15
2,7	1,6				
4,5	2,5				
6,0	3,0				
8,1	4,5				
8,8	5,3				
10,0	6,0				
11,4	6,8				
12,0	7,2				
13,8	8,3			±0,3	
15,0	9,0				
19,0	11,4	±0,4		0,90	±0,25
30,0	15,0	±2,0	±0,5	1,2	±0,5
40,0	20,0	±3,0	±0,6	1,5	±0,6

The setting of the TCT and CCT tubes is held at the temperatures from 175°C to 230°C